

High-Accuracy Digimatic Micrometer

The world's first 5 μ m micrometer

(Based on Mitutoyo's data valid as of June 2011.)

.000005"

Resolution



- Enabling 5 μ m (0.1 μ m) resolution measurement, this micrometer is ideal for customers who need to make highly accurate measurements with a hand-held tool.

- The High-Accuracy Digimatic Micrometer utilizes Mitutoyo's innovative 5 μ m (0.1 μ m) resolution ABS (absolute) rotary sensor*¹ and high-accuracy screw machining technology to reduce the instrumental error to ± 0.00002 " (0.5 μ m), delivering higher accuracy without sacrificing operability.

*1. Patent pending in Japan, the United States of America, the European Union, and China.

- A highly rigid frame and high-performance constant-force mechanism*² enable more stable measurement, while the clicks emitted while the workpiece is being measured assures the operator that measurement is proceeding normally.

*2. Patent pending in Japan, the United States of America, the European Union, and China.

- Body heat transferred to the instrument is reduced by a (removable) heat shield, minimizing the error caused by thermal expansion of the frame when performing handheld measurements.

- The ABS (absolute) rotary sensor*³ eliminates the need to perform origin setting each time the power is turned on, letting you start measuring straight away. With no possibility of overspeed errors, the High-Accuracy Digimatic Micrometer also delivers a higher level of reliability.

ABSOLUTE
Absolute System Patented by MITUTOYO

*3. Patent pending in Japan, the United States of America, the European Union, and China.

- The High-Accuracy Digimatic Micrometer has a range of features to enable flexible measurement, including switchable resolution .000005"/.00002" (0.0001mm/0.0005mm), function lock and preset.

Specifications

	Metric	Inch/Metric
Code No.	293-100	293-130
Measuring range	0 - 25mm	0 - 1" / 0 - 25.4mm
Resolution	0.0001mm/0.0005mm (switchable)	.000005"/.00002" 0.0001mm/0.0005mm (switchable)
Instrumental error (20°C)* ⁴	$\pm 0.5\mu$ m	± 0.00002 "
Measuring surface	$\varnothing 3.2$ mm	
Measuring force	7 to 9 N	
Measuring system	Electromagnetic induction type ABS rotary sensor	
Mass	400 g (440 g with heat shield attached)	
Power supply	Lithium battery (CR2032) x 1	
Battery life	Approx. two years when used under normal conditions	

*4. Includes quantization error of ± 1 count.



Function lock


Mitutoyo

High-Accuracy Digimatic Micrometer



293-130

Dimensions



Standard accessories

Heat shield (No.04AAB969A: 293-100
No.04AAB969B: 293-130) x 1
Lithium battery (CR2032: for the monitor) x 1
Spanner (No.200877) x 1

Screwdriver (No.04AAB985) x 1
Lens paper (for the monitor)
Inspection certificate



With heat shield*5
attached



*5. Patent pending in Japan, the United States of America, the European Union, and China.

Functions

Preset (ABS measurement system): The measurement origin can be preset to any value within the display range for convenience in measuring.

Zero-setting: (INC measurement system): The display can be zeroed at any position of the spindle, making comparison measurement easier. Returning to the absolute-measurement mode is easily accomplished.

Hold: The displayed value is held while the spindle is withdrawn and the micrometer moved so that the display can be read at the operator's convenience. After cancelling the hold, the instrument returns to the previous measuring mode (absolute or incremental).

Resolution switching: The resolution of the display can be switched. If 5µin(0.1µm) measurement is not required, the resolution can be switched to .00002\"(0.5µm).

Function lock: Functions such as preset or zero-set can be locked to avoid inadvertently changing the origin position.

On/off: The power can be turned off after measurement is complete. Even after the power is turned off, the origin or last zero-set position remains in the memory.

Auto power off: Even if the power is left on, the power turns off automatically if the micrometer is not used within a 20-minute period.

Measurement data output: Measurement data can be output, allowing easy incorporation of this instrument into a statistical process control or measurement system.

Error alarm: In the unlikely event of a display overflow or calculation error, an error message is displayed and measurement stops. Measurement cannot continue until the error is corrected.

Also, if the battery voltage drops below a certain point, the battery indicator will turn on before measurement becomes impossible, warning the user that the battery needs to be replaced.



Coordinate Measuring Machines

Vision Measuring Systems

Form Measurement

Optical Measuring

Sensor Systems

Testing Equipment and
Seismometer

Digital Scale and DRO Systems

Small Tool Instruments and
Data Management

Mitutoyo America Corporation
www.mitutoyo.com

One Number to Serve You Better
1-888-MITUTOYO (1-888-648-8869)

M³ Solution Centers

Aurora, Illinois

(Corporate Headquarters)

Westford, Massachusetts

Huntersville, North Carolina

Mason, Ohio

Plymouth, Michigan

City of Industry, California

Mitutoyo
Precision is our Profession

Note: All information regarding our products, and in particular the illustrations, drawings, dimensional and performance data contained in this printed matter as well as other technical data are to be regarded as approximate average values. We therefore reserve the right to make changes to the corresponding designs. The stated standards, similar technical regulations, descriptions and illustrations of the products were valid at the time of printing. In addition, the latest applicable version of our General Trading Conditions will apply. Only quotations submitted by ourselves may be regarded as definitive.

Mitutoyo products are subject to US Export Administration Regulations (EAR). Re-export or relocation of Mitutoyo products may require prior approval by an appropriate governing authority.

Trademarks and Registrations

Designations used by companies to distinguish their products are often claimed as trademarks. In all instances where Mitutoyo America Corporation is aware of a claim, the product names appear in initial capital or all capital letters. The appropriate companies should be contacted for more complete trademark and registration information.

We reserve the right to change specifications and prices without notice.

© 2012 Mitutoyo America Corporation, Aurora IL

0212-04 • Printed in USA • February 2012