



HANDYSURF+

35 | 40 | 45

New HANDYSURF+, reborn with sophisticated design
Portable surface texture measuring instrument for global use responding
to diverse everyday needs

HANDYSURF+ **NEW**



High resolution with wide measuring range No need to set up measuring range

The previous HANDYSURF required setting of a narrow measuring range when measuring with a high resolution, but HANDYSURF+ has evolved! The instrument has the Z direction measuring range of 370 μm , which is the widest in class, and achieved a resolution as high as 0.0007 μm over the entire range.



Select from 3 HANDYSURF+ driver units, according to workpiece and measurement location



35 (Standard type)

The standard-type measurable with different attitudes including horizontal, inclined, vertical and ceiling surfaces.



40 (Retract type)

Retract-type that reduces damage to the stylus and pickup by raising the pickup while waiting for measurement or at ending. It can be used as a detector incorporated into an automatic machine.



45 (transverse trace-type)


The transverse trace-type where the pickup moves sideways. Narrow areas, such as crankshaft pins and journals, that were difficult to measure before can now be measured.

Connectable to the compact printer, USB memory stick and PC with built-in USB connector

With the USB connector, it is possible to print measurement results to the optional compact printer, save measurement conditions and results on USB memory sticks and recharge the instrument from the USB port of a PC or with a USB battery.



Compact Printer (Option)



By connecting to the USB memory stick (option), it is possible to save and read measurement conditions and results.


Superior Operability

2.4 inch color LCD has significantly improved the visibility.

Moreover, 6 buttons and newly developed UI have achieved simple and intuitive operations.



Home screen




Menu screen



Measurement condition setting display

Multiple analysis capabilities


Graphic representation of measurement results enables their on-site verification with parameter and waveform. Moreover, despite being a portable instrument, it is capable of a variety of analyses including analyses of BAC, ADC, peak count and motifs. By setting the conditions in advance, OK/NG judgment can be performed automatically.




Example of surface roughness (Ra) measurement



Example of OK/NG judgment of measurement result



Example of BAC analysis



Example of ADC analysis

Display available in 20 languages

Multi-language support available worldwide

20 European and Asian languages including English, German and French are provided as standard. Display language can be easily and quickly changed by menu options.



English



German



French



Italy



Spanish



Portuguese



Czech



Polish



Hungarian



Turkish



Swedish



Dutch



Japanese



Chinese
Traditional Chinese
Simplified Chinese



Korean



Thai



Malay



Vietnamese



Indonesian





Specifications

Model			HANDYSURF ⁺				
			35		40		45
			Tip radius 5 μm	Tip radius 2 μm	Tip radius 5 μm	Tip radius 2 μm	Tip radius 5 μm
Measurement range	Z direction		-210 to +160 μm				
	Drive axis		X direction 16 mm				Y direction 4 mm
Tracing Driver	Movement type		Standard type		Retraction type		Horizontal tracing type
	Evaluation Length		0.2 to 16 mm				
	Measurement speed		0.5, 0.6, 0.75, 1.0 mm/s				
Pickup	Sensing type		Differential inductance				
	Measurement Method		Skid				
	Z direction resolution		0.0007 μm/-210 to +160 μm				
	Model		E-DT-SM10A	E-DT-SM49A	E-DT-SM10A	E-DT-SM49A	E-DT-SM39A
	Stylus	Measurement force	4 mN	0.75 mN	4 mN	0.75 mN	4 mN
		Tip radius	r _{tip} = 5 μm	r _{tip} = 2 μm	r _{tip} = 5 μm	r _{tip} = 2 μm	r _{tip} = 5 μm
		Tip angle	90°cone	60°cone	90°cone	60°cone	90°cone
		tip material	Diamond				
Analysis item	Calculation Standards		Comply with JIS2013/2001, JIS1994, JIS1982, ISO1997/2009, ISO13565, DIN1990, ASME2002/2009, ASME1995, CNOMO				
	Parameter	Profile Curve	Pt, Rmax, Rz, Rk, Rpk, Rvk, Mr1, Mr2, Vo, K, tp				
		Roughness Curve	Ra, Rq, Rz, Rv, Rc, Rt, RSm, RΔq, Rsk, Rku, Rmr(c), Rmr, Rδc, Rz94, R3z, RΔa, Ry, Sm, S, tp, PC, RPc JIS, RPc ISO, RPc EN, Pc, PPI, Rp, Rmax, Mr1, Mr2, Rpk, Rvk, Rk, Vo, K, A1, A2, Rpm, Δa, Δq, Htp				
		Motif	R, Rx, AR, W, Wx, AW, Rke, Rpke, Rvke, NCRX, NR, CPM, SR, SAR, Wte, NW, SAW, SW, Mr1e, Mr2e, Vo, K				
	Evaluation Curve		Profile Curve, Roughness Curve, ISO13565Special Roughness Curve, Roughness motif curve, Waviness motif curve, Upper envelope waviness curve				
Filter	Characteristics graph		Bearing area curve, Amplitude distribution curve				
	Filter type		Gaussian, 2RC (phase compensation), 2RC (non-phase compensation)				
	Cutoff value	λc	0.08, 0.25, 0.8, 2.5 mm				
Amplification indicator	λs		None, 2.5, 8 μm				
	Display		2.4-inch color liquid crystal panel				
	Data output	USB connectors for USB memory/printer connection x 1, Micro USB connector for USB communication x 1					
	Print output	Optional (external printer unit) / Thermal recording paper width: 58 mm (recording width: 48 mm)					
Specifications	Language		English, German, French, Italian, Spanish, Portuguese, Czech, Polish, Hungarian, Turkish, Swedish, Dutch, Japanese, Chinese (Traditional Chinese/Simplified Chinese), Korean, Thai, Malay, Vietnamese, Indonesian,				
	Power Supply	Charging	Built-in battery (to be charged using AC adaptor, PC USB port, USB battery), charging period: 4 hours (about 1000 measurements can be take when fully charged)				
		Voltage, frequency	AC100 to 240 V ±10%, 50/60 Hz, Single phase (Included AC adapter)				
		Power consumption	Maximum 10 W				
	External dimensions (W x D x H) / Weight		Amplification indicator: 184.5 x 68 x 57.4 mm/about 500 g for the entire svstem				



Together with our partners, we are able to offer you a Europe-wide sales and service network. Through the regional proximity, a service technician can reach your premises without any prolonged wait and travel times. If you have any questions, please contact us directly from all European countries through our centralized metrology phone number or email address:



+49(0)89 54 6788 - 0

Mon – Fri from 8:30 a.m. to 5:00 p.m.



sf-g-info@accretech.eu

Germany

Carl Zeiss 3D Metrology
Services GmbH Stuttgart
Felix-Wankel-Str. 6
73760 Ostfildern
www.zeiss.de/messtechnik-stuttgart
Email stuttgart.metrology.de@zeiss.com
Tel. +49 (0)711 3416 78-10

Austria

ACCRETECH (Europe) GmbH
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +49 (0)89 54 6788 - 0

Switzerland

ACCRETECH (Europe) GmbH
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +49 (0)89 54 6788 - 0

Osterwalder Messtechnik AG
Sumpfstraße 13
6312 Steinhausen
www.osterwalder-zug.ch
Email info@osterwalder-zug.ch
Tel. +41 (0)41 748 19 19

Italy

ACCRETECH (Europe) GmbH
Via Giotto, 7
20032 Cormano
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +39 02 2316 3291

France

ACCRETECH (Europe) GmbH
14 Chemin des Clos
38240 Meylan
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +33 (0)476 0440 80

United Kingdom

Bowers Group
Unit 3, Albany Court
Albany Park, Camberley
Surrey, GU16 7QR
www.bowersgroup.co.uk
Email sales@bowersgroup.co.uk
Tel. +44 (0)12 7646 9866

Ireland

JED Metrology Ltd.
21 Tolka Valley Business Park
Glasnevin, Dublin 11
Email sales@jed.ie
Tel. +353 1 830 7744

Denmark

Carl Zeiss AS
Blokken 76, 3460 Birkerød
www.zeiss.dk
Email info.metrology.dk@zeiss.com
Tel. +45 7015 7015

Sweden

ACCRETECH (Europe) GmbH
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +49 (0)89 54 6788 - 0

Norway

Carl Zeiss AS
Kabelgaten 8, 0580 Oslo
www.zeiss.no
Email info.metrology.no@zeiss.com
Tel. +47 2317 2390

Finland

Carl Zeiss Oy
IMT Finland, Niittyvillankuja 4B
01510 Vantaa
www.zeiss.fi
Email info.metrology.fi@zeiss.com
Tel. +358 (0) 20794 0891

Netherlands

ACCRETECH (Europe) GmbH
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +49 (0)89 54 6788 - 0

Spain

Izasa Scientific S.L.U.
Plaza Europa 21-23
08908 L'Hospitalet de Llobregat,
Barcelona
www.izasascientific.com
Email marketing@izasascientific.com
Tel. +34 902 20 30 80

Portugal

Izasa Scientific, LDA
Rua do Proletariado, 1
Quinta do Paizinho
2790-138 Carnaxide, Lisboa
www.izasascientific.com
Email marketing@izasascientific.com
Tel. +351 21 424 73 18

Poland

ACCRETECH (Europe) GmbH
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +49 (0)89 54 6788 - 0

Hungary

ACCRETECH (Europe) GmbH
Liget utca 3/2 3. Floor
2040 Budaörs, Hungary
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +36 23 232 224

Bulgaria

ACCRETECH (Europe) GmbH
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +49 (0)89 54 6788 - 0

Romania

Mark Dimension Technologies S.R.L
Sos. Stefan cel Mare Nr. 14
Building 19
Apartment 46
020141 Bucharest
www.markd.ro
Email office@markd.ro
Tel. +40 724 629953

Slovakia

ACCRETECH (Europe) GmbH
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +49 (0)89 54 6788 - 0

Slovenia

ACCRETECH (Europe) GmbH
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +49 (0)89 54 6788 - 0

Czech Republic

ACCRETECH (Europe) GmbH
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +49 (0)89 54 6788 - 0

Turkey

ACCRETECH (Europe) GmbH
www.accretech.eu
Email sf-g-info@accretech.eu
Tel. +49 (0)89 54 6788 - 0

We reserve the right to change the contents of this catalog, including product specifications, without notice when products are updated. Some of our products shall be controlled by the Foreign Exchange and Foreign Trade Act, and required an export license by the Japanese Government. Regarding exporting the products and/or providing a non-resident with technologies, please consult ACCRETECH (Tokyo Seimitsu).



EUROPE

ACCRETECH (Europe) GmbH
Landsberger Str. 396, 81241 Munich, Germany
Phone +49 (0)89 54 67 88 - 0, Fax +49 (0)89 54 67 88 - 10
sf-g-info@accretech.eu
www.accretech.eu